

Specifications



Photo is representative



Eaton R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton rotary disconnect switch |
| CATALOG NUMBER | R5A3040U |
| UPC | 786685402888 |
| PRODUCT LENGTH/DEPTH | 2.57 in |
| PRODUCT HEIGHT | 3.35 in |
| PRODUCT WIDTH | 1.77 in |
| PRODUCT WEIGHT | 0.5 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | CCC Marked |
| CERTIFICATIONS | CSA Certified EN Listed IEC Rated UL 508 |
| CATALOG NOTES | Suitable as motor disconnect |



Powering Business Worldwide

Physical Attributes

| | |
|-----------------|------------|
| NUMBER OF POLES | Three-pole |
| SERIES | R5 |

Performance Ratings

| | |
|-----------------|-------|
| AMPERAGE RATING | 40A |
| VOLTAGE RATING | 600 V |

Miscellaneous

| | |
|------------------|---------------|
| PRODUCT CATEGORY | Rotary Switch |
|------------------|---------------|

Resources

| | |
|-------------------------------|---|
| CATALOGS | Commercial Distribution, Switching Devices, Volume 2, Tab 1 |
| MULTIMEDIA | Switching Devices Flex Center |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - R5A3040U |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton rotary disconnect switch |
| CATALOG NUMBER | R5A3040U |
| UPC | 786685402888 |
| PRODUCT LENGTH/DEPTH | 2.57 in |
| PRODUCT HEIGHT | 3.35 in |
| PRODUCT WIDTH | 1.77 in |
| PRODUCT WEIGHT | 0.5 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | CCC Marked |
| CERTIFICATIONS | CSA Certified EN Listed IEC Rated UL 508 |
| CATALOG NOTES | Suitable as motor disconnect |



Powering Business Worldwide

Physical Attributes

| | |
|-----------------|------------|
| NUMBER OF POLES | Three-pole |
| SERIES | R5 |

Performance Ratings

| | |
|-----------------|-------|
| AMPERAGE RATING | 40A |
| VOLTAGE RATING | 600 V |

Miscellaneous

| | |
|------------------|---------------|
| PRODUCT CATEGORY | Rotary Switch |
|------------------|---------------|

Resources

| | |
|-------------------------------|---|
| CATALOGS | Commercial Distribution, Switching Devices, Volume 2, Tab 1 |
| MULTIMEDIA | Switching Devices Flex Center |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - R5A3040U |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

