



## RECESSED TAMPER-RESISTANT DUPLEX OUTLET

R885TRWCC6 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Recessed Duplex Tamper-Resistant Outlet. Great for Flat Screen TV's, Furniture pinch points, Kitchen Counters and more. 15 amp, 125 volt, White.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



### PRODUCT ENVIRONMENTAL PROFILE

- Recessed Duplex Tamper-Resistant Outlet
- Installs on finished wall in standard electrical boxes
- Appliance plugs remain recessed behind wall surface
- Great for Flat Screen TV's, Furniture pinch points, Kitchen Counters and more
- Tamper-Resistant meets NEC code
- Integral wall plate
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Tamper-Resistant

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121704

#### DIMENSIONS

Depth (US): 1.85"

Height (US): 4.7"

Width (US): 2.9"

**TECHNICAL INFORMATION**

Amps: 15A

Volts: 125

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No



## RECESSED TAMPER-RESISTANT DUPLEX OUTLET

R885TRWCC6 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Recessed Duplex Tamper-Resistant Outlet. Great for Flat Screen TV's, Furniture pinch points, Kitchen Counters and more. 15 amp, 125 volt, White.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



### PRODUCT ENVIRONMENTAL PROFILE

- Recessed Duplex Tamper-Resistant Outlet
- Installs on finished wall in standard electrical boxes
- Appliance plugs remain recessed behind wall surface
- Great for Flat Screen TV's, Furniture pinch points, Kitchen Counters and more
- Tamper-Resistant meets NEC code
- Integral wall plate
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Tamper-Resistant

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121704

#### DIMENSIONS

Depth (US): 1.85"

Height (US): 4.7"

Width (US): 2.9"

**TECHNICAL INFORMATION**

Amps: 15A

Volts: 125

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No