



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RCD38TRW Radiant SP/3WAY SW+15A TR Outlet WH

*Pass & Seymour/Legrand*

Catalog Number	RCD38TRW
Manufacturer	Pass & Seymour/Legrand
Description	A Step Up From Ordinary, This Combination Switch and Outlet From The Radiant® Collection Provides Convenience and Flexibility, As Well As Style. Operable In Both Single-Pole and 3-Way Applications, You Can Use It Alone to Control One Light or Fixture, or Use With Another 3-Way Switch For Controlling The Light From Two Locations. Also Includes A Tamper-Resistant Outlet For Safe Access to The Basic Power Every Home Needs. Part Of The Radiant® Collection, It Features Clean Lines and A Smooth Finish For A Soph
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

### Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Outlet Type	Tamper-Resistant
Poles	3-Way, 1
Switch Type	Push
Voltage	120.0 V
Voltage Rating	125
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Color	White
Finish	Matte

### Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	RADIANT SP/3WAY SW+15A TR OUTLET WH
extra long description	P&S RCD38TRW RADIANT SP/3WAY SW+15A
Features	Locator Light, Combination
Long Description	A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a soph
Product Type	Radiant SP/3WAY SW+15A TR Outlet WH
Special Features	Single Pole 3-Way Switch

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007055085
Manufacturers Part Number	RCD38TRW
UPC	785007055085

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Switch, Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	12
Weight Per each	0.2083

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	Flammability Rating: UL 94 V2
Mounting	BOX
nema rating	15A
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	CULUS, UL, cULus, UL Listed