



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **RCL153PNLHWH Dalia Led+ 150W Led 600W Inc WNL White Clam** *Lutron*

Catalog Number	RCL153PNLHWH
Manufacturer	Lutron
Description	Dalia Led+ Dimmer, 120 V, Rotary Knob, UL1472 / Csa C22.2 184.1, Nom, White, Clamshell
Weight per unit	0.2800 (lbs/each)
Product Category	Lighting

### Features

media	Yes
Voltage Rating	120

### Material, Color, and Finish

Color	White
Finish	Gloss

### Dimensions and Weight

Size	4.60 x 2.86
------	-------------

### Descriptions

Description	DALIA LED+ 150W LED 600W INC WNL WHITE CLAM
extra long description	LUT RCL-153PNLH-WH DALIA LED+ DIMME
Features	The Lutron Dalia LED+ dimmer switch combines a classic rotary style with Lutron's LED+ Advanced Technology and is rated for 150W dimmable LED bulbs or 600W incandescent/halogen bulbs. Toggle the lights on/off by pushing on the knob or rotate the knob to dim/brighten lights. The soft glow locator light, under the knob, helps you find the Dalia dimmer switch in the dark. The Dalia's versatile design allows you to swap out a variety of wall plate and knob colors to complement any application. This dimmer does
Long Description	Dalia LED+ Dimmer, 120 V, Rotary Knob, UL1472 / CSA C22.2 184.1, NOM, White, Clamshell
Product Type	Dalia Led+ Dimmer White Clamshell

### Manufacturer Information

Brand	Lutron
GTIN	00784276281379
Manufacturers Part Number	RCL-153PNLH-WH
UPC	784276281379

### Taxonomies, Classifications, and Categories

Type	Dimmer for dimmable LED, Halogen, Incandescent, and CFL bulbs.
------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.28

## Uses, Certifications, and Standards

Application	Lighting Control
standard	UL1472 / CSA C22.2 184.1, NOM