



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RCD33BK Radiant 2 SW SP/3WAY + SP/3WAY BK

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | RCD33BK  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Control Two Separate Lights or Devices From A Single Location With This Combination Switch. Both Switches Feature Installation Flexibility, Usable For Single-Pole or 3-Way Applications. Designed to Emulate The Sleek Lines Of The Collection'S Paddle Switches, It Delivers Flexible, Space-Saving Control With The Sophisticated Look Of Radiant. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately. |
| Weight per unit  | 0.2083 (lbs/each)  |
| Product Category | Gen Purpose Switches   |

### Features

|                       |                     |
|-----------------------|---------------------|
| actuator              | Rocker switch       |
| amperage rating       | 15                  |
| Contact Configuration | 15A                 |
| Contact Rating        | 15 Amp, 120/125 VAC |
| media                 | Yes                 |
| Mounting Type         | Box                 |
| Number of Gangs       | 1.0                 |
| Number of Switches    | 2.0                 |
| operating cycles      | 50000               |
| Poles                 | 3-Way, 1            |
| Switch Type           | Push                |
| Voltage               | 120.0 V             |
| Voltage Rating        | 120                 |
| Wire Size             | #14 - #10 Awg       |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|      |  |
|------|--|
| Size | Depth 1.43" x Width 1.29" x Height 3.81" |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | RADIANT 2 SW SP/3WAY + SP/3WAY BK  |
| extra long description | P&S RCD33BK RADIANT 2 SW, SP/3WAY +  |
| Features               | Combination, Locator Light   |
| Long Description       | Control two separate lights or devices from a single location with this combination switch. Both switches feature installation flexibility, usable for single-pole or 3-way applications. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. |
| Product Type           | Radiant 2 SW, SP/3WAY + SP/3WAY BK   |
| Special Features       | The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. Unique "Up/Down" switches match the look and feel of radiant paddle switches.   |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007054934         |
| Manufacturers Part Number | RCD33BK                |
| UPC                       | 785007054934           |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | SWITCH             |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 12     |
| Weight Per each | 0.2083 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Residential                              |
| environmental conditions | UL94 V2                                  |
| Mounting                 | BOX                                      |
| Operating Temperature    | Maximum continuous +115°C, minimum -40°C |
| standard                 | UL, CULUS, cULus, UL Listed              |