

# Eaton RJDN250

Catalog Number: RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton enclosed circuit breaker	RJDN250
<b>UPC</b>	<b>Product Length/Depth</b>
786679256145	10.22 in
<b>Product Height</b>	<b>Product Width</b>
37.5 in	11.88 in
<b>Product Weight</b>	<b>Warranty</b>
37 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	With Knockouts

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

125-250A

### Circuit breaker type

JD, JDB, HJD, JDC

### Enclosure

NEMA 3R

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - RJDN250](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton RJDN250

Catalog Number: RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton enclosed circuit breaker	RJDN250
<b>UPC</b>	<b>Product Length/Depth</b>
786679256145	10.22 in
<b>Product Height</b>	<b>Product Width</b>
37.5 in	11.88 in
<b>Product Weight</b>	<b>Warranty</b>
37 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	With Knockouts

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

125-250A

### Circuit breaker type

JD, JDB, HJD, JDC

### Enclosure

NEMA 3R

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - RJDN250](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)