

Eaton RJDN250

Catalog Number: RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface



General specifications

| | |
|--------------------------------|--|
| Product Name | Catalog Number |
| Eaton enclosed circuit breaker | RJDN250 |
| UPC | Product Length/Depth |
| 786679256145 | 10.22 in |
| Product Height | Product Width |
| 37.5 in | 11.88 in |
| Product Weight | Warranty |
| 37 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Certifications | Catalog Notes |
| UL Listed CSA Certified | With Knockouts |

Product specifications

Type

Circuit Breaker Enclosure

Amperage Rating

125-250A

Circuit breaker type

JD, JDB, HJD, JDC

Enclosure

NEMA 3R

Series

Series C

Mounting Method

Surface mounting

Resources

Catalogs

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

Specifications and datasheets

[Eaton Specification Sheet - RJDN250](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton RJDN250

Catalog Number: RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface



General specifications

| | |
|--------------------------------|--|
| Product Name | Catalog Number |
| Eaton enclosed circuit breaker | RJDN250 |
| UPC | Product Length/Depth |
| 786679256145 | 10.22 in |
| Product Height | Product Width |
| 37.5 in | 11.88 in |
| Product Weight | Warranty |
| 37 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Certifications | Catalog Notes |
| UL Listed CSA Certified | With Knockouts |

Product specifications

Type

Circuit Breaker Enclosure

Amperage Rating

125-250A

Circuit breaker type

JD, JDB, HJD, JDC

Enclosure

NEMA 3R

Series

Series C

Mounting Method

Surface mounting

Resources

Catalogs

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

Specifications and datasheets

[Eaton Specification Sheet - RJDN250](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia