



OLD WORK SWITCH AND OUTLET BOX WITH QUICK/CLICK

S118W | [Pass & Seymour](#)

FEATURES & BENEFITS

Durable, impact-resistant thermoplastic box complemented by innovative extras that cut installation time. Single Gang, Old Work Switch and Outlet Box with Swing-Bracket for mounting. Adjusts from 1 1/4" down to 1/8". Two Auto/Clamps on Each End. 100 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 2 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Metal swing bracket for quick mounting in existing walls.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater
Type: Switch, Outlet Box
Special Features: Old Work, Quick/Click

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
Federal Spec: No
UL Standard: Yes
UN SPSC: 39121308

DIMENSIONS

Depth (US): 3.03125"

Height (US): 3.75"

Width (US): 2.25"

TECHNICAL INFORMATION

Material: Plastic

NEMA Configuration Number: OS2

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





OLD WORK SWITCH AND OUTLET BOX WITH QUICK/CLICK

S118W | [Pass & Seymour](#)

FEATURES & BENEFITS

Durable, impact-resistant thermoplastic box complemented by innovative extras that cut installation time. Single Gang, Old Work Switch and Outlet Box with Swing-Bracket for mounting. Adjusts from 1 1/4" down to 1/8". Two Auto/Clamps on Each End. 100 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 2 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Metal swing bracket for quick mounting in existing walls.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Type: Switch, Outlet Box

Special Features: Old Work, Quick/Click

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

Federal Spec: No

UL Standard: Yes

UN SPSC: 39121308

DIMENSIONS

Depth (US): 3.03125"

Height (US): 3.75"

Width (US): 2.25"

TECHNICAL INFORMATION

Material: Plastic

NEMA Configuration Number: OS2

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

