



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12010CT00 2" SS304 Emt, 10' Calbrite

| | |
|------------------|---|
| Catalog Number | S12010CT00 |
| Manufacturer | Calbrite |
| Description | Emt Stainless Steel 304 Conduit 2" 10 Feet Long |
| Weight per unit | 14.8 (lbs/each) |
| Product Category | Emt (Electrical MC) |

Features

| | |
|------------------|------------------------|
| Inside Diameter | 2 |
| Material | Stainless Steel - 304L |
| outside diameter | 2.2 |
| Wall Thickness | 0.1 |

Material, Color, and Finish

| | |
|--------|--------------------|
| Color | Polished Silver |
| Finish | #4 Polished Finish |

Dimensions and Weight

| | |
|--------|-----|
| Length | 120 |
|--------|-----|

Descriptions

| | |
|------------------------|---|
| Description | 2" SS304 EMT, 10' |
| extra long description | CAL S12010CT00 2" X 10' SS304 EMT |
| Features | Stainless steel EMT conduit and fittings combine strength with ductility, resulting in an affordable, lightweight and easy-to-handle conduit assembly. EMT can be installed indoors and outdoors in accordance with UL and NEC® requirements. |
| Long Description | EMT Stainless Steel 304 Conduit 2" 10 Feet Long |
| Product Type | 2" X 10' SS304 Emt |
| Short Description | SS_EMT_304 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | CALBRITE |
| GTIN | 00847656002527 |
| Manufacturers Part Number | S12010CT00 |
| UPC | 847656002527 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | Stainless Steel EMT Conduit |
| Type | EMT |

Trade Size

| | |
|------------|---|
| Trade Size | 2 |
|------------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 10

Packaging

Carton 10

Weight 2.40

Weight Per foot 14.8

Uses, Certifications, and Standards

Temperature Rating 1600