



## 4 INCH ROUND CEILING BOX

S120RAC | [Pass & Seymour](#)

### FEATURES & BENEFITS

4" Round Ceiling Box with two captive mounting nails and four Auto/Clamps. It is constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive. Its depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling. 50 pack.



- Auto/Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fixture support -- max weight rating 50 lbs.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Size: 4"  
Type: Ceiling Box

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121308

UR: No

## DIMENSIONS

Depth (US): 2.1875

Diameter (US): 4

Volume: 20.25

## TECHNICAL INFORMATION

Material: Plastic

Mounting: Captive mounting nails

Shape: round

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





## 4 INCH ROUND CEILING BOX

S120RAC | [Pass & Seymour](#)

### FEATURES & BENEFITS

4" Round Ceiling Box with two captive mounting nails and four Auto/Clamps. It is constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive. Its depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling. 50 pack.



- Auto/Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fixture support -- max weight rating 50 lbs.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Size: 4"  
Type: Ceiling Box

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121308

UR: No

## DIMENSIONS

Depth (US): 2.1875

Diameter (US): 4

Volume: 20.25

## TECHNICAL INFORMATION

Material: Plastic

Mounting: Captive mounting nails

Shape: round

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

