



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S100X125VAM 1X1-1/4" Self-Laminating LBL Cass

Panduit Corporation

Catalog Number	S100X125VAM
Manufacturer	Panduit Corporation
Description	The S100X125VAM Die-Cut Self-Laminating Label Cassette Includes Both Label Material and Ribbon For Easy Changeover. Self-Laminating Adhesive Labels For Wire/Cable Identification Include A White Print-On Area and A Clear Overlaminates. For Use With The MP300 Printer. Vinyl. 1" X 1.25" (25.4 MM X 31.8 MM). Wire/Cable Size Range 12 - 10 Awg. Color Clear/White. 200 Labels Per Cassette. 1 Cassette Per Package.
Weight per unit	1.0 (lbs/each)
Product Category	Tools & Testers

Features

Material	Vinyl
maximum temperature	150
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Width	1
-------	---

Descriptions

Description	1X1-1/4" SELF-LAMINATING LBL CASS
extra long description	PAN S100X125VAM PXE™ S100X125VAM MP
Long Description	The S100X125VAM Die-Cut Self-Laminating Label Cassette includes both label material and ribbon for easy changeover. Self-laminating adhesive labels for wire/cable identification include a white print-on area and a clear overlaminates. For use with the MP300 printer. Vinyl. 1" x 1.25" (25.4 mm x 31.8 mm). Wire/Cable Size Range 12 - 10 AWG. Color Clear/White. 200 labels per cassette. 1 cassette per package.
Product Type	Pxe™ S100X125VAM MP Printer Self-Lam Label, Vinyl, White, 1.

Manufacturer Information

Brand	PANDUIT
GTIN	00613056761353
Manufacturers Part Number	S100X125VAM
UPC	613056761353



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Self-Laminating Label

Packaging

Carton	1
Weight Per each	1.03

Uses, Certifications, and Standards

standard	RoHS Compliant
----------	----------------