



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S10N06A07N 7.5KVA Buck Boost Transformer 1PH 120X240-16/32V

Eaton Corp

| | |
|------------------|---|
| Catalog Number | S10N06A07N |
| Manufacturer | Eaton Corp |
| Description | Eaton General Purpose Encapsulated Transformer, Buck-Boost General-Purpose Encapsulated Transformer, Ep, Aluminum, Nema 3R, 178, 60 HZ, Single-Phase, 120 V, 240 V, 16/32 V, None, 115 °C Rise, 7.5 Kva, Indoor-Outdoor, 509B |
| Weight per unit | 123.0 (lbs/each) |
| Product Category | 20081031151214 |

Features

| | |
|-------------------|-------------------------------------|
| connection | 509B |
| design | EP |
| dimensions | 9.8900 IN X 10.3800 IN X 16.0000 IN |
| frame | 178 |
| Number of Phases | Single-phase |
| Primary Voltage | 120 V, 240 V |
| Secondary Voltage | 16/32 V |

Descriptions

| | |
|------------------------|---|
| Description | 7.5KVA BUCK BOOST TRANSFORMER 1PH 120X240-16/32V |
| extra long description | ETN S10N06A07N 7.5KVA Buck Boost TX |
| Features | Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA. |
| Long Description | Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 178, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 7.5 KVA, indoor-outdoor, 509B |
| Product Type | 7.5KVA Buck Boost TX 1PH 120X240-16/32V |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00786680103490 |
| Manufacturers Part Number | S10N06A07N |
| UPC | 786680103490 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | BUCK & BOOST TRANSFORMERS |
| Type | Encapsulated transformer |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 123 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| Frequency Rating | 60 Hz |
| standard | UL Listed |
| Temperature Rating | 115 °C rise |