

### Heavy duty grade power plugs & adapters

#### Product description

2-pole, 3-wire grounding  
 30A, 125/250V/AC  
 50A, 125/250V/AC





TT-30R

#### Design features

- Terminals have pressure plates to protect wires
- 83 accepts #12 - #10 AWG wire
- 1264 adapts travel trailer plug to female 15A or 20A, 125V/AC NEMA 5-15R or 5-20R receptacle

#### Power plugs & adapters

Rating	A	V/AC	NEMA	Description	Color	Catalog no.		
30	125	TT-30P	Angled power plug, matching receptacle 1263	BK	□ 83	•	•	
			Travel trailer receptacle to NEMA 5-15/5-20P plug adapter	BK	□ 1264 <sup>A</sup>	•		

<sup>A</sup> Not UL listed. 83: Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified



83



1264



S41



S42

### Heavy duty grade power plugs & adapters

#### Product description

2-pole, 3-wire grounding  
 30A, 125V/AC; 30A, 250V/AC  
 50A, 125V/AC; 50A, 250V/AC



5-30P



5-50R



6-30R





6-50R

#### Design features



- Universal plugs include blades for both 30A and 50A configurations of the same voltage
- Bodies made of durable thermoplastic
- Terminals have pressure plates to protect wires
- Accepts #10 - #6 AWG wire

#### Universal power plugs

Rating	A	V/AC	NEMA	Description	Color	Catalog no.		
30	125	5-30P/5-50P	Universal power plug, matching receptacle 1233	BK	□ S41	•	•	
			Angled power plug, matching receptacle 1253					

Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified

#### Universal power plugs

Rating	A	V/AC	NEMA	Description	Color	Catalog no.		
30	250	6-30P/6-50P	Universal power plug; matching receptacles 1232, 1234	BK	□ S42	•	•	
			Angled power plug; matching receptacles 1252, 1254					

Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified

#### Color ordering information:

BK (Black)



(Black)

**Dimensional information:** B-70 **Specification information:** Please visit [www.eaton.com/wiringdevices](http://www.eaton.com/wiringdevices)  
**Compliances, specifications and availability are subject to change without notice.**

 Indicates NAFTA compliant - Page G-21

 RoHS compliant - Page G-21

### Heavy duty grade power plugs & adapters

#### Product description

2-pole, 3-wire grounding  
 30A, 125/250V/AC  
 50A, 125/250V/AC





TT-30R

#### Design features

- Terminals have pressure plates to protect wires
- 83 accepts #12 - #10 AWG wire
- 1264 adapts travel trailer plug to female 15A or 20A, 125V/AC NEMA 5-15R or 5-20R receptacle

#### Power plugs & adapters

Rating	A	V/AC	NEMA	Description	Color	Catalog no.		
30	125	TT-30P		Angled power plug, matching receptacle 1263	BK	□ 83	•	•
				Travel trailer receptacle to NEMA 5-15/5-20P plug adapter	BK	□ 1264 <sup>A</sup>	•	

<sup>A</sup> Not UL listed. 83: Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified



83



1264



S41



S42

### Heavy duty grade power plugs & adapters

#### Product description

2-pole, 3-wire grounding  
 30A, 125V/AC; 30A, 250V/AC  
 50A, 125V/AC; 50A, 250V/AC



5-30P



5-50R



6-30R





6-50R

#### Design features



- Universal plugs include blades for both 30A and 50A configurations of the same voltage
- Bodies made of durable thermoplastic
- Terminals have pressure plates to protect wires
- Accepts #10 - #6 AWG wire

#### Universal power plugs

Rating	A	V/AC	NEMA	Description	Color	Catalog no.		
30	125	5-30P/5-50P		Universal power plug, matching receptacle 1233	BK	□ S41	•	•
				Angled power plug, matching receptacle 1253				

Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified

#### Universal power plugs

Rating	A	V/AC	NEMA	Description	Color	Catalog no.		
30	250	6-30P/6-50P		Universal power plug; matching receptacles 1232, 1234	BK	□ S42	•	•
				Angled power plug; matching receptacles 1252, 1254				

Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified

#### Color ordering information:

BK (Black)



(Black)

**Dimensional information:** B-70 **Specification information:** Please visit [www.eaton.com/wiringdevices](http://www.eaton.com/wiringdevices)  
**Compliances, specifications and availability are subject to change without notice.**

 Indicates NAFTA compliant - Page G-21

 RoHS compliant - Page G-21