



S3942

60A19/CL/VS
60 watt A19 Incandescent; Clear; 2500 average rated hours;
580 lumens; Medium base; 130 volts; 2/Pack

Features

- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3942

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|--------------|-------|------------|--------|-----------|-------------|---------|
| S3942 | 045923039423 | 60 | A19 | Medium | E26 | 60A19/CL/VS | 130 |

| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Average Rated Hours | Pack | Package Type |
|--------|---------------|---------------|----------|----------------|---------------------|------|--------------|
| Clear | 4 1/8" | 2.38" | C-9 | 580 | 2500 | 120 | 2pk |

| RoHS Compliant |
|----------------|
| Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3942

60A19/CL/VS
60 watt A19 Incandescent; Clear; 2500 average rated hours;
580 lumens; Medium base; 130 volts; 2/Pack

Features

- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3942

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|--------------|-------|------------|--------|-----------|-------------|---------|
| S3942 | 045923039423 | 60 | A19 | Medium | E26 | 60A19/CL/VS | 130 |

| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Average Rated Hours | Pack | Package Type |
|--------|---------------|---------------|----------|----------------|---------------------|------|--------------|
| Clear | 4 1/8" | 2.38" | C-9 | 580 | 2500 | 120 | 2pk |

| RoHS Compliant |
|----------------|
| Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

