



S5839

MS250/ED28 /PS /U /4K
250 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5839

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|------------------|---------------------|----------------|----------------|------------|-----------------------|
| S5839 | 045923058394 | 250 | ED28 | Mogul | E39 | M153/E | MS250/ED28 /PS /U /4K |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color | Pulse Start |
| Clear | 8.31" | 3.50" | 15000 | 25000 | 4000 | Cool White | Yes |
| Pack | CRI | Burning Position | | | RoHS Compliant | | |
| 12 | 65 | Universal | | | Yes | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5839

MS250/ED28 /PS /U /4K
250 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5839

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|------------------|---------------------|----------------|----------------|------------|-----------------------|
| S5839 | 045923058394 | 250 | ED28 | Mogul | E39 | M153/E | MS250/ED28 /PS /U /4K |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color | Pulse Start |
| Clear | 8.31" | 3.50" | 15000 | 25000 | 4000 | Cool White | Yes |
| Pack | CRI | Burning Position | | | RoHS Compliant | | |
| 12 | 65 | Universal | | | Yes | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

