



S7217

13T2/27
13 watt; Mini Spiral Compact Fluorescent; 2700K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7217

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|--------------|---------------|-------------------------------|----------------|-------------------------|------------------|--------------------------------|-----------|
| S7217 | 045923072178 | 120 | 13 | 60W | T2 | Medium | E26 |
| Lamp Code | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 13T2/27 | 4.13" | 1.81" | 900 | 12000 | 2700 | Warm White | 48/12 |
| Package Type | CRI | CEC Status | Hg Content | RoHS Compliant | UL or ETL Listed | Warranty | |
| Box | 82 | Lawful for sale in California | 1.6 mg | Yes | Yes | 2 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7217

13T2/27
13 watt; Mini Spiral Compact Fluorescent; 2700K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7217

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|--------------|---------------|-------------------------------|----------------|-------------------------|------------------|--------------------------------|-----------|
| S7217 | 045923072178 | 120 | 13 | 60W | T2 | Medium | E26 |
| Lamp Code | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 13T2/27 | 4.13" | 1.81" | 900 | 12000 | 2700 | Warm White | 48/12 |
| Package Type | CRI | CEC Status | Hg Content | RoHS Compliant | UL or ETL Listed | Warranty | |
| Box | 82 | Lawful for sale in California | 1.6 mg | Yes | Yes | 2 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

