

# Eaton S811+N37N3S

Catalog Number: S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta



## General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+N37N3S
UPC	Product Length/Depth
786685558899	11 in
Product Height	Product Width
11.5 in	9 in
Product Weight	Certifications
7.8 lb	Contact Manufacturer

**Amperage Rating**

37A

**Special features**

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

**Type**

Severe duty

**Frame size**

N

**Rating**

10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

**Application notes**

S8xL adjustment - Switching from S801+ to S811+

**Brochures**

S811+/S801+ soft starters

**Catalogs**

Product Range Catalog Drives Engineering

Product Datasheet - S811+N37N3S

Eaton's Volume 2—Commercial Distribution

**Drawings**

Type S811+ Soft Starter - N-frame

**Installation instructions**

Instructions for S811+ Soft Starter, S811+N... and S811+R

**Multimedia**

Soft Starter Product Family Overview

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

**Specifications and datasheets**

Eaton Specification Sheet - S811+N37N3S

**Warranty guides**

Selling Policy 25-000 - Distribution and Control Products and Services

# Eaton S811+N37N3S

Catalog Number: S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta



## General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+N37N3S
UPC	Product Length/Depth
786685558899	11 in
Product Height	Product Width
11.5 in	9 in
Product Weight	Certifications
7.8 lb	Contact Manufacturer

**Amperage Rating**

37A

**Special features**

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

**Type**

Severe duty

**Frame size**

N

**Rating**

10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

**Application notes**

S8xL adjustment - Switching from S801+ to S811+

**Brochures**

S811+/S801+ soft starters

**Catalogs**

Product Range Catalog Drives Engineering

Product Datasheet - S811+N37N3S

Eaton's Volume 2—Commercial Distribution

**Drawings**

Type S811+ Soft Starter - N-frame

**Installation instructions**

Instructions for S811+ Soft Starter, S811+N... and S811+R

**Multimedia**

Soft Starter Product Family Overview

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

**Specifications and datasheets**

Eaton Specification Sheet - S811+N37N3S

**Warranty guides**

Selling Policy 25-000 - Distribution and Control Products and Services