



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC50 1/2" Flex Conn D/C Squeeze Type

Appleton/Oz Gedney

| | |
|------------------|---|
| Catalog Number | SC50 |
| Manufacturer | Appleton/Oz Gedney |
| Description | Features:1.35IN Dia X 1.5IN Length, 0.48 In Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.5IN, Connection:Male NPS Thread, Material:Zinc Die Cast |
| Weight per unit | 0.1000 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|-----------------|
| angle | Straight |
| connection | Male NPS Thread |
| Connector Type | Squeeze |
| insulation | Non Insulated |
| Material | Zinc Die Cast |

Material, Color, and Finish

| | |
|--------|----------|
| Color | Metallic |
| Finish | Natural |

Dimensions and Weight

| | |
|------|-----|
| Size | 0.5 |
|------|-----|

Descriptions

| | |
|------------------------|---|
| Description | 1/2" FLEX CONN D/C SQUEEZE TYPE |
| extra long description | EGS SC-50 1/2 IN SQUEEZE CONN FLEX/ |
| Long Description | Features:1.35IN Dia X 1.5IN Length, 0.48 IN Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.5IN, Connection:Male NPS Thread, Material:Zinc Die Cast |
| Product Type | 1/2 In Squeeze Conn Flex/Ac |
| Special Features | 1.35 IN Dia X 1.5 IN Length, 0.48 IN Thread Length, Flexible Metal Conduit |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | APPOZGCOMM |
| GTIN | 00687855200504 |
| Manufacturers Part Number | SC-50 |
| UPC | 687855200504 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | Straight Squeeze Connector |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 0.5

Availability

Status Inactive

Packaging

Carton 25

Package 250

Weight Per each 0.1

Uses, Certifications, and Standards

Application Terminates flexible metal conduit to a knockout in a dry location
box or enclosure

environmental conditions Dry Location

nema rating FB-1

standard UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No.
18.3, CSA Certified: 208044; NEMA: FB-1