



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SCR15GFSTSW Satin Color 15A Receptacle Self-Testing Gfci Snow *Lutron*

Catalog Number	SCR15GFSTSW
Manufacturer	Lutron
Description	Lutron Claro Tamper-Resistant Gfci Duplex Receptacle, 15-Amp, Snow
Weight per unit	0.3400 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Screw Terminal
insulation	Plastic
Number of Wires	3;4;5
Poles	2
Voltage Rating	125
Wattage	1875
Wire Size	10 to 14

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	SATIN COLOR 15A RECEPTACLE SELF-TESTING GFCI SNOW
extra long description	LUT SCR-15-GFST-SW SC 15A GFCI SELF
Features	Coordinate Lutron lighting controls and switches with Lutron Claro receptacles to complement your clients' decor. This self-testing GFCI receptacle automatically checks every 30 seconds to see if critical components are damaged and GFCI protection is lost. There is an LED status indicator that provides peace of mind as well as a permanently installed internal tamper-resistant shutter mechanism, capable of resisting insertion of foreign elements into the receptacle openings. Install with screw terminals or
Long Description	Lutron Claro Tamper-Resistant GFCI Duplex Receptacle, 15-Amp, Snow
Product Type	SC 15A Gfci Self Testing Snow
Special Features	Self-testing technology allows GFCI to automatically check proper operation every 30 seconds. LEDs indicate status of GFCI protection function. Press reset button to reset GFCI after circuit interruption. Wallplate sold separately.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276159067
Manufacturers Part Number	SCR15GFSTSW
UPC	784276159067

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	GFCI receptacle

Packaging

Carton	1
Package	24
Weight Per each	0.34

Uses, Certifications, and Standards

Application	Lighting Control
environmental conditions	0 to 90% humidity, non-condensing
Mounting	WALLBOX
nema rating	5-15R
standard	UL, CSA, NOM, NEC, CEC, OSHA