

# Eaton SF500PH10X10

Catalog Number: SF500PH10X10

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3

## General specifications



### Product Name

Eaton rotary disconnect shaft extension

### Catalog Number

SF500PH10X10

### UPC

786685408538

### Product Length/Depth

19.7 in

### Product Height

0.39 in

### Product Width

0.39 in

### Product Weight

0.85 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Photo is representative

### Certifications

Contact Manufacturer

## Physical Attributes

### Series

R9

### Type

Shaft extension

## Performance Ratings

### Amperage Rating

100-400A

## Miscellaneous

### Product Category

Shaft extensions for external handles

### Size

500 mm (19.7 in)

### Special features

Shaft for PH2 handle, I-,J-,K-,L-,M-frame

### Used with

Handle type: PH2, PH3

## Resources

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - SF500PH10X10](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton SF500PH10X10

Catalog Number: SF500PH10X10

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3

## General specifications



### Product Name

Eaton rotary disconnect shaft extension

### Catalog Number

SF500PH10X10

### UPC

786685408538

### Product Length/Depth

19.7 in

### Product Height

0.39 in

### Product Width

0.39 in

### Product Weight

0.85 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Photo is representative

### Certifications

Contact Manufacturer

## Physical Attributes

### Series

R9

### Type

Shaft extension

## Performance Ratings

### Amperage Rating

100-400A

## Miscellaneous

### Product Category

Shaft extensions for external handles

### Size

500 mm (19.7 in)

### Special features

Shaft for PH2 handle, I-,J-,K-,L-,M-frame

### Used with

Handle type: PH2, PH3

## Resources

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - SF500PH10X10](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)