



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SE125PSCLR0 1-1/4" BLK Expn Sleeve, 50' Roll

Panduit Corporation

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | SE125PSCLR0 |
| Manufacturer | Panduit Corporation |
| Description | Fray Resistant Braided Expandable Sleeving, 1.25" (31.8 MM) Diameter, Can Be Cut With A Pair Of Scissors and Provides Continuous Abrasion Resistance For Wires, Cables, and Tubing. The Lightweight, Durable Protection Is Flexible and The Open Weave Will Not Trap Heat or Humidity. Polyethylene Terephthalate. 50 FT (15.2 M) Reel. Color Black. |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Cable Ties & Wraps |

Features

| | |
|--------------|------|
| Material | PET |
| media | Yes |
| Nominal Size | 1.25 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|----------|-------------|
| Diameter | 1.00 - 1.50 |
| Length | 50 |

Descriptions

| | |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 1-1/4" BLK EXPN SLEEVE,50' ROLL |
| extra long description | PAN SE125PSC-LR0 Pan-Wrap™ SE125PSC |
| Long Description | Fray resistant braided expandable sleeving, 1.25" (31.8 mm) diameter, can be cut with a pair of scissors and provides continuous abrasion resistance for wires, cables, and tubing. The lightweight, durable protection is flexible and the open weave will not trap heat or humidity. Polyethylene Terephthalate. 50 ft (15.2 m) reel. Color Black. |
| Product Type | Pan-Wrap™ SE125PSC-LR0 Fray Resistant Sleeving, Black, Pet, |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983816934 |
| Manufacturers Part Number | SE125PSC-LR0 |
| UPC | 074983816934 |

Taxonomies, Classifications, and Categories

| | |
|------|-----------------------------|
| Type | Braided Expandable Sleeving |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per roll 1.07

Uses, Certifications, and Standards

Application (1) Fray-Resistant Design Resists Fraying when Cut with Scissors;
..... (2) Provides Continuous Abrasion Protection Resistance for
..... Wires, Cables, and Tubing;

standard CSA Certified, Compliant with U.S. and European passenger rail
..... standards, UL Recognized E116868; RoHS Compliant

Temperature Rating 257