

Eaton SF500PH10X10

Catalog Number: SF500PH10X10

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3

General specifications



Photo is representative

Product Name	Catalog Number
Eaton rotary disconnect shaft extension	SF500PH10X10
UPC	Product Length/Depth
786685408538	19.7 in
Product Height	Product Width
0.39 in	0.39 in
Product Weight	Warranty
0.85 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
Contact Manufacturer	

Physical Attributes

Series

R9

Type

Shaft extension

Performance Ratings

Amperage Rating

100-400A

Miscellaneous

Product Category

Shaft extensions for external handles

Size

500 mm (19.7 in)

Special features

Shaft for PH2 handle, I-,J-,K-,L-,M-frame

Used with

Handle type: PH2, PH3

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

SF500PH10X10 AutoCAD 2D Footprint

SF500PH10X10 2D PDF

SF500PH10X10 2D Drawing Xchange

SF500PH10X10 3D Model Xchange

SF500PH10X10 AutoCAD 2D Footprint (mm)

SF500PH10X10 3D Inventor

Multimedia

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - SF500PH10X10

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton SF500PH10X10

Catalog Number: SF500PH10X10

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3

General specifications



Photo is representative

Product Name	Catalog Number
Eaton rotary disconnect shaft extension	SF500PH10X10
UPC	Product Length/Depth
786685408538	19.7 in
Product Height	Product Width
0.39 in	0.39 in
Product Weight	Warranty
0.85 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
Contact Manufacturer	

Physical Attributes

Series

R9

Type

Shaft extension

Performance Ratings

Amperage Rating

100-400A

Miscellaneous

Product Category

Shaft extensions for external handles

Size

500 mm (19.7 in)

Special features

Shaft for PH2 handle, I-,J-,K-,L-,M-frame

Used with

Handle type: PH2, PH3

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

SF500PH10X10 AutoCAD 2D Footprint

SF500PH10X10 2D PDF

SF500PH10X10 2D Drawing Xchange

SF500PH10X10 3D Model Xchange

SF500PH10X10 AutoCAD 2D Footprint (mm)

SF500PH10X10 3D Inventor

Multimedia

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - SF500PH10X10

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)