



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SGB382CL 3/4" Diecast Mighty-Right Split Ground Bushing

Bridgeport Fittings

| | |
|------------------|---|
| Catalog Number | SGB382CL |
| Manufacturer | Bridgeport Fittings |
| Description | Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 3/4 Inch |
| Weight per unit | 0.2080 (lbs/each) |
| Product Category | Aluminum |

Features

| | |
|----------|------------|
| Material | Zinc Alloy |
| media | Yes |

Material, Color, and Finish

| | |
|--------|---------------------------|
| Color | Grey with Black Insulator |
| Finish | Ball burnish |

Dimensions and Weight

| | |
|------|-----|
| Size | 3/4 |
|------|-----|

Descriptions

| | |
|------------------------|--|
| Description | 3/4" DIECAST MIGHTY-RIGHT SPLIT GROUND BUSHING |
| extra long description | BPT SGB-382CL 3/4" SPLT GND BSH LUG |
| Features | Split Bushings install after the wire pull. No more burning through bushings or fighting with pullers. Save time and effort too! |
| Long Description | Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 3/4 Inch |
| Product Type | 3/4" SPLT GND BSH Lug 4-14 Awg |
| Special Features | Grounding Lug Wire Capacity # 14 - #4 |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747903822 |
| Manufacturers Part Number | SGB-382CL |
| UPC | 781747903822 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs |
| Type | SPLIT |

Trade Size

| | |
|------------|------|
| Trade Size | 0.75 |
|------------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.208 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated bushing is required. Grounding lug; aluminum alloy 60610-T6. Rated 150 Degree C. cULus listed. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations! |
| standard | cULus |
| Temperature Rating | 150°C |