



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **SHC1052 Cordcon, STR ML, 1.00-1.13", 1 1/4", Alu** *Hubbell Wiring Devices*

Catalog Number	SHC1052
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Cord Connectors, Straight Male, 1.00-1.13", 1 1/4", Aluminum
Weight per unit	1.2 (lbs/each)
Product Category	Cable & Cord Grips

### **Features**

Material	Aluminum, Cast
Number of Conductors	Single
pallet quantity	3150

### **Material, Color, and Finish**

Color	Metallic
-------	----------

### **Dimensions and Weight**

Size	1 1/4" NPT
------	------------

### **Descriptions**

Description	CORDCON, STR ML, 1.00-1.13", 1 1/4", ALU
extra long description	HWDK SHC1052 CORDCON, STR ML, 1.00-
Features	Cord Connectors - Hubbell has the broadest line and the widest choice of materials in the industry. NPT hub sizes from 1/4" to 3" in straight male end, 90°, 45°, female and underground feed connectors. They are available in your choice of aluminum, plated steel, nylon and stainless steel. The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and oth
Long Description	Kellems Wire Management, Cord Connectors, Straight Male, 1.00-1.13", 1 1/4", Aluminum
Product Type	Cordcon, STR ML, 1.00-1.13", 1 1/4", Alu
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585200521
Manufacturers Part Number	SHC1052
series	Standard Duty
UPC	783585200521



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	STRAIGHT MALE

## Packaging

Carton	1
Package	10
Weight Per each	1.2

## Uses, Certifications, and Standards

Application	Straight Male- Form 5
environmental conditions	Suitable for use in wet locations when used with a listed nylon washer between box and fitting.
Mounting	Locknut or Tapped Opening
nema rating	12;4;4X;NEMA Type 4, 4X, 12 and 13
standard	UL Listed
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)