






Shovels

FEATURES:

- 48" Handle Tensioned Fiberglass
- Minimum Breaking Strength of 261 Lbs Per DTH6950-1
- Safe From Electrical Shock
- Does Not Absorb Moisture
- Resists Industrial Chemicals
- Ergonomically Designed Grip
- Standard Or D Handle
- Made In The USA



The shovel and grip ends are larger to provide leverage and control while the center tapers to help your hand slide when "slinging" the material away from the hole.



BSE#	DOTTIE#	DESCRIPTION	HANDLE LENGTH	STD	MSTR	WT/STD	UNIT
XXXXXX	SHR	#2 Round Point	48" Handle	1	5	5.05#	Ea
XXXXXX	SHS	#2 Square Point	48" Handle	1	5	5.44#	Ea
XXXXXX	SHD	14" Drain Spade	48" Handle	1	5	4.84#	Ea
XXXXXX	SHDSS	14" Sharpshooter	27" 'D' Handle	1	5	3.77#	Ea
XXXXXX	SHTR4	4" Trenching	48" Handle	1	5	4.31#	Ea
XXXXXX	SHTR5	5" Trenching	48" Handle	1	5	5.20#	Ea
XXXXXX	SPH	Post Hole Digger	48" Handle	1	5	11.94#	Ea



L.H. Dottie Company
 Commerce, CA 90040
 lhdottie.com




Shovels

FEATURES:

- 48" Handle Tensioned Fiberglass
- Minimum Breaking Strength of 261 Lbs Per DTH6950-1
- Safe From Electrical Shock
- Does Not Absorb Moisture
- Resists Industrial Chemicals
- Ergonomically Designed Grip
- Standard Or D Handle
- Made In The USA



The shovel and grip ends are larger to provide leverage and control while the center tapers to help your hand slide when "slinging" the material away from the hole.



BSE#	DOTTIE#	DESCRIPTION	HANDLE LENGTH	STD	MSTR	WT/STD	UNIT
XXXXXX	SHR	#2 Round Point	48" Handle	1	5	5.05#	Ea
XXXXXX	SHS	#2 Square Point	48" Handle	1	5	5.44#	Ea
XXXXXX	SHD	14" Drain Spade	48" Handle	1	5	4.84#	Ea
XXXXXX	SHDSS	14" Sharpshooter	27" 'D' Handle	1	5	3.77#	Ea
XXXXXX	SHTR4	4" Trenching	48" Handle	1	5	4.31#	Ea
XXXXXX	SHTR5	5" Trenching	48" Handle	1	5	5.20#	Ea
XXXXXX	SPH	Post Hole Digger	48" Handle	1	5	11.94#	Ea

L.H. Dottie Company
 Commerce, CA 90040
 lhdottie.com