



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SMIC0100AC 120V Ac/DC Smoke/CO Combo W/Silence - UI 217 8TH

*BRK Brands/Ademco/First Alert*

Catalog Number	SMIC0100AC
Manufacturer	BRK Brands/Ademco/First Alert
Description	Hardwired Combo Smoke & CO Alarm With Replaceable Battery Backup. Ac 120V Interconnectable With Silence and Latching Features. Includes Ionization Smoke Sensing Technology, Electrochemical Carbon Monoxide Sensor and A 9V Alkaline Battery.
Weight per unit	0.5700 (lbs/each)
Product Category	Builders Products

### Features

dimensions	1.9 in 5.6 in 5.6 in
------------	----------------------

### Material, Color, and Finish

Color	White
-------	-------

### Descriptions

Description	120V AC/DC SMOKE/CO COMBO W/SILENCE - UL 217 8TH
extra long description	BRK 1046871 Smoke and CO Alarm
Features	Combo Smoke and CO Alarm
Long Description	Hardwired Combo smoke & CO Alarm with replaceable battery backup. AC 120V Interconnectable with Silence and Latching features. Includes Ionization smoke sensing technology, electrochemical carbon monoxide sensor and a 9V alkaline battery.
Product Type	Alarm Combo Ac/DC SMICO100-Ac Box
Short Description	Combo Smoke and CO Alarm
Special Features	Battery Backup,End-of-Life Warning,Hardwire Interconnectivity,Hardwire Quick Connect Plug Included,Precision Detection

### Manufacturer Information

Brand	BRK
GTIN	00029054022974
Manufacturers Part Number	1046871
UPC	029054022974

### Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	Combination Smoke & Carbon Monoxide Alarm



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.57

## Uses, Certifications, and Standards

standard	Conforms to UL 217 8th Edition Standard, Conforms to STD UL2034
----------	--