



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP18W Plastic Wallplate 2G Toggle Duplex W/Out Line WH

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | SP18W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Combination Wall Plate, 1 Toggle Switch and 1 Duplex Receptacle, 2-Gang |
| Weight per unit | 0.1183 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|------------------------------------|
| cutout | Toggle and Receptacle |
| insulation | Bare |
| media | Yes |
| Mounting Type | Exposed Screws |
| Number of Gangs | 2 |
| orientation | Vertical |
| Wall Plate Type | Combination, Dimmer/Switch, Outlet |

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|---|
| Description | PLASTIC WALLPLATE 2G TOGGLE DUPLEX W/OUT LINE WH |
| extra long description | P&S SP18W PLATE PLST 2G TOG/DUP W/O |
| Long Description | Combination Wall Plate, 1 Toggle Switch and 1 Duplex Receptacle, 2-Gang |
| Product Type | Plate PLST 2G Tog/Dup W/Out Line WH |
| Special Features | Standard size plastic smooth wall plate |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007681536 |
| Manufacturers Part Number | SP18-W |
| UPC | 785007681536 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 200 |
| Weight Per each | 0.1183 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CSA, CSA, UL514 |