Pass and Seymour

1-Gang Thermoset Wall Plate, 1 Duplex Receptacle Opening, White

Part No. SP8W



Plastic Plate, single gang, duplex without line is molded of non-combustible mar-proof material. It is resistant to discoloration, grease, oil, solvent, and moisture. The seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Features & Benefits

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Nominal thickness, .070 inch.

Individually wrapped with color-matching screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007680379
Country Of Origin	Mexico	Material	Thermoset Plastic
Construction	Plastic	Wall Plate Size	Standard Size
Wall Plate Type	Duplex Receptacle	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695

Additional Information

Product Environmental Profile	Yes

Technical Information

Thickness	0.07 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		

Pass and Seymour

1-Gang Thermoset Wall Plate, 1 Duplex Receptacle Opening, White

Part No. SP8W



Plastic Plate, single gang, duplex without line is molded of non-combustible mar-proof material. It is resistant to discoloration, grease, oil, solvent, and moisture. The seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Features & Benefits

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Nominal thickness, .070 inch.

Individually wrapped with color-matching screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007680379
Country Of Origin	Mexico	Material	Thermoset Plastic
Construction	Plastic	Wall Plate Size	Standard Size
Wall Plate Type	Duplex Receptacle	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695

Additional Information

Product Environmental Profile	Yes

Technical Information

Thickness	0.07 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		