



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

SSC38B 3/8"-16 Concrete Bottom Mount Rod Hanger

L.H. Dottie CO.

Catalog Number	SSC38B
Manufacturer	L.H. Dottie CO.
Description	Concrete Bottom Mount Rod Hanger, Steel Material, Zinc Plated Finish, 1-1/2 In. Length, 1/4 X 1-1/2 In. Size, 1/4 In. Diameter, Ansi Wedge Bolt Thread
Weight per unit	0.0450 (lbs/each)
Product Category	Anchors & Fasteners

Features

Material	Steel
Tensile Strength	1475

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Diameter	1/4
Length	1-1/2
Size	1/4 X 1-1/2

Descriptions

Description	3/8"-16 CONCRETE BOTTOM MOUNT ROD HANGER
extra long description	DOTTIE SSC38B 3/8" Concrete Drillin
Long Description	Concrete Bottom Mount Rod Hanger, Steel material, Zinc Plated Finish, 1-1/2 in. length, 1/4 x 1-1/2 in. Size, 1/4 in. diameter, ANSI Wedge Bolt Thread
Product Type	3/8" Concrete Drilling Rod Hanger (Bottom Mount)
Special Features	Features: Self-Tapping, Bottom Mount

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002185505
Manufacturers Part Number	SSC38B
UPC	781002185505

Taxonomies, Classifications, and Categories

Category Description	ANCHORS & ANCHOR KITS
Type	Concrete Bottom Mount Rod Hanger

Packaging

Carton	100
Weight Per each	0.045



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Concrete, Pipe Hanging, Conduit, Eye Rod, Cable Trays, Lighting Systems, Strut Channels, Overhead Utilities, Sprinkler Systems, Drop Ceilings, HVAC Duct, Electrical, Refrigeration

standard

C/US UL Listed, Factory Mutual Approval - File Number J.I. 3015153