

Specifications



Photo is representative

Eaton STL131A120CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, 13-jaw, Pre-wired test switch, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	STL131A120CH
UPC	786685703404
PRODUCT LENGTH/DEPTH	5.3 in
PRODUCT HEIGHT	21.8 in
PRODUCT WIDTH	12.6 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Austin Energy Approved, transformer rated



Product specifications

TYPE	Transformer rated socket
-------------	--------------------------

Resources

AMPERAGE RATING	20A
FEED TYPE	Bottom
NUMBER OF JAWS	13-jaw
VOLTAGE RATING	600 V
ACCESSORIES	Pre-wired test switch
NUMBER OF SOCKETS	1

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - STL131A120CH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative

Eaton STL131A120CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, 13-jaw, Pre-wired test switch, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	STL131A120CH
UPC	786685703404
PRODUCT LENGTH/DEPTH	5.3 in
PRODUCT HEIGHT	21.8 in
PRODUCT WIDTH	12.6 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Austin Energy Approved, transformer rated



Product specifications

TYPE	Transformer rated socket
-------------	--------------------------

Resources

AMPERAGE RATING	20A
FEED TYPE	Bottom
NUMBER OF JAWS	13-jaw
VOLTAGE RATING	600 V
ACCESSORIES	Pre-wired test switch
NUMBER OF SOCKETS	1

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - STL131A120CH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

