

Specifications

Photo is representative

Eaton T47

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, T shape, 1-1/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T47
UPC	782274627502
PRODUCT LENGTH/DEPTH	7.44 in
PRODUCT HEIGHT	3.19 in
PRODUCT WIDTH	2.31 in
PRODUCT WEIGHT	2.85 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	T
TRADE SIZE	1-1/4"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification
INSTALLATION INSTRUCTIONS	IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T47 Condulet Form 7 Industrial Grade Conduit Bodies
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications

Photo is representative

Eaton T47

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, T shape, 1-1/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T47
UPC	782274627502
PRODUCT LENGTH/DEPTH	7.44 in
PRODUCT HEIGHT	3.19 in
PRODUCT WIDTH	2.31 in
PRODUCT WEIGHT	2.85 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	T
TRADE SIZE	1-1/4"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification
INSTALLATION INSTRUCTIONS	IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T47 Condulet Form 7 Industrial Grade Conduit Bodies
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.