



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T3000FC Wireless K-Type Temperature FC

Fluke Electronics

| | |
|------------------|---|
| Catalog Number | T3000FC |
| Manufacturer | Fluke Electronics |
| Description | The Fluke 3000 FC Wireless Test Tools Are A Team and The Modules Are Team Players. You Connect Any Of The Fluke Connect™ Modules to Your Test Point and Then View The Results On Specific Fluke Connect Enabled Hardware or Through Windows® Software On Your PC—Up to 20 Meters (65.6 Feet) Away. Save Time and Conduct More Tests With Less Trips. Fluke T3000 FC Wireless K-Type Temperature Module. A Versatile K-Type Thermocouple Thermometer Wirelessly Relays Measurements to Other Fluke Connect™ Enabled Master Units |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Test Equipment - Multimeters |

Features

| | |
|---------------|---|
| Response Time | 1 |
|---------------|---|

Descriptions

| | |
|------------------------|---|
| Description | WIRELESS K-TYPE TEMPERATURE FC |
| extra long description | FLK FLK-T3000FC FC WIRELESS K-TYPE |
| Long Description | The Fluke 3000 FC Wireless Test Tools are a team and the modules are team players. You connect any of the Fluke Connect™ Modules to your test point and then view the results on specific Fluke Connect enabled hardware or through Windows® software on your PC—up to 20 meters (65.6 feet) away. Save time and conduct more tests with less trips. Fluke t3000 FC Wireless K-Type Temperature Module. A versatile K-type thermocouple thermometer wirelessly relays measurements to other Fluke Connect™ enabled master units |
| Product Type | FC Wireless K-Type Temperature Mod |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | FLUKE |
| GTIN | 00095969692021 |
| Manufacturers Part Number | FLK-T3000FC |
| UPC | 095969692021 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
|----------------------|---|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 1.1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|---------------------------------------|---|
| Enclosure environmental conditions | Hard plastic RF communication range--Open air, unobstructed: Up to 20 m; Obstructed, sheetrock wall: Up to 6.5 m; Obstructed, concrete wall or steel electrical enclosure: Up to 3.5 m; Operating temperature -10 °C to +50 °C, Storage temperature -40 °C to +60 °C |
| Temperature Rating | K-type: -200 °C to 1372 °C |