



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390



T81248G8CCTHYB 12W Led T8 48" 3K/35K/4K/5K/65K Combo Tube Glass Rab Lighting

Catalog Number	T81248G8CCTHYB
Manufacturer	Rab Lighting
Description	T8 12W 1650 Lumens 4FT Glass Type A+B S/D 5CCT 120-277V
Weight per unit	0.4400 (lbs/each)
Product Category	Lighting

Features

average life	50000
Ballast Type	UL Type A+B, Hybrid
Base	G13
beam angle	220
Fixture Type	Linear Tubes
lumens	1,650
Shape	T8
total harmonic distortion	<25%
Voltage Rating	Type A: Ballast dependent; Type B: 120-277
Wattage	12

Material, Color, and Finish

Color	White
color rendering index (cri)	>80
color temperature	3000/3500/4000/5000/6500
Finish	Matte

Dimensions and Weight

Length	4
--------	---

Descriptions

Description	12W LED T8 48" 3K/35K/4K/5K/65K COMBO TUBE GLASS
extra long description	RAB T8-12-48G-8CCT-HYB T8 12W 14FT
Long Description	T8 12W 1650 LUMENS 4FT GLASS TYPE A+B S/D 5CCT 120-277V
Product Type	T8 12W 14FT Glass Type A+B S/D 5CCT Unv
Special Features	Direct replacement for fluorescent lamps: F32T8/32W, F32T8/30W, F32T8/28W, F32T8/25WTYPE A - plug-and-play compatible with most common commercial T8 electronic ballastsTYPE B - can be wired directly to line voltage 120-277V. Can be wired using single- or double-ended methodWorks with both shunted and non-shunted sockets5 color temperatures in 1 SKU (3000K, 3500K, 4000K, 5000K, 6500K)50,000-Hour lifespan



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00192552024587
Manufacturers Part Number	T8-12-48G-8CCT-HYB
UPC	192552024587

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Tubes

Packaging

Carton	1
Package	25
Weight Per each	0.44

Uses, Certifications, and Standards

Application	Indoor Lamps
-------------	--------------