
Mounting Bases, Cable Ties and Accessories

Convenient one-piece design!

Ty-Rap® Tie for Panel and Chassis Mounting



- One-piece design, fast and convenient to use
- Clamping range of 1/16 to 23/8 inches reduces your inventory - one clamp replaces many
- · Visually attractive head resembles rivet
- Locking grooves maintain tight grip
- Lowers your installed cost



STD. CAT. NO.	BULK CAT. NO.	BODY WIDTH IN./MM	LENGTH IN./MM	MAX. WIRE BUNDLE DIA. IN./MM	HOLE SIZE IN./MM	STRENGTH LBS./N	STD. PKG. QTY.	BULK PKG. QTY.
TY541M	TY41M	.23/5.84	9.60/243.84	2.37/60.20	.3268/8.13-17.27	65/289.10	50	1,000
650-41600	_	.23/5.84	10.25/260.35	2.50/63.50	.3268/8.13-17.27	65/289.10	500	1,000
696-41848	_	.23/5.84	12.50/317.50	3.00/76.20	.3268/8.13-17.27	65/289.10	500	1,000

Note: Loop tie through hole in frame, around electrical, hydraulic, or air hoses to be clamped, and through head. Tighten and cut off with Ty-Rap tool. Visually looks like a rivet.


- For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).
- · Black color

Choose from adhesive-backed, epoxy or screw mounting bases!

Two-Way Adhesive Mounting Bases

- Available in a variety of materials for both indoor and outdoor use
- One-piece molding no lost parts
- Adhesive-backed with pressuresensitive adhesive tape (where applicable)





STD. PKG. CAT. NO.	BULK PKG. Cat. No.	MOUNTING METHOD	MAX. TIE WIDTH ACCOM.	LENGTH IN./MM	WIDTH IN./MM	MATERIAL	STD. PKG. QTY.	BULK PKG.
TC5342A	TC342A	SRA* Adhesive	.19	1.13/28.58	1.13/28.58	Nylon 6.6	100	1,000
_	TC342A-X	SRA* Adhesive	.19	1.13/28.58	1.13/28.58	UV Black	_	1,000
_	TC342	TC2PA [†]	.19	1.13/28.58	1.13/28.58	Nylon 6.6	_	1,000
_	TC342X	TC2PA [†]	.19	1.13/28.58	1.13/28.58	UV Black	_	1,000
_	TC342A-FR	SRA* Adhesive	.19	1.13/28.58	1.13/28.58	Flame-Retardant Nylon	_	1,000
_	TC342AH-TFR	Acrylic Adhesive	.19	1.13/28.58	1.13/28.58	Black High-Temp Flame-Retardant Nylon	_	1,000

Temperature Rating: 32° F to 120° F (0° C to 48° C)

*Synthetic Rubber Adhesive

†TC2PA Adhesive sold separately

Note: See product expiration date on package. Periodically check product for adhesion and replace as needed. Product is for wire management only and is not intended for use as a primary support of wire, cable, etc.



Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 **Technical Services** Tel: 888.862.3289

