Specifications







Eaton TCFH100N

Eaton Bussmann series TCFH modular fuse holder, Electrical panelboards, Machinery disconnects, Industrial control, Required finger safe systems, 100 A, Class CF, Glass filled PBT, Panel, 600 Vac/dc, Low-peak finger safe fuse

General specifications	
PRODUCT NAME	Eaton Bussmann series TCFH modular fuse holder
CATALOG NUMBER	TCFH100N
UPC	051712223508
PRODUCT LENGTH/DEPTH	2.91 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed

Powering Business Worldwide

Electrical rating

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac, 600 Vdc

Physical details

MATERIAL	Glass filled PBT

General information

CLASS	Class CF
MOUNTING METHOD	Panel
USED WITH	low-peak finger safe fuse

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2209
MULTIMEDIA	The Power of Space Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TCFH100N
TECHNICAL DATA SHEETS	TCFH100N~CUBFUSE 100 AMP HOLDER HIGH PROFILE
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

Specifications







Eaton TCFH100N

Eaton Bussmann series TCFH modular fuse holder, Electrical panelboards, Machinery disconnects, Industrial control, Required finger safe systems, 100 A, Class CF, Glass filled PBT, Panel, 600 Vac/dc, Low-peak finger safe fuse

General specifications	
PRODUCT NAME	Eaton Bussmann series TCFH modular fuse holder
CATALOG NUMBER	TCFH100N
UPC	051712223508
PRODUCT LENGTH/DEPTH	2.91 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed

Powering Business Worldwide

Electrical rating

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac, 600 Vdc

Physical details

MATERIAL	Glass filled PBT

General information

CLASS	Class CF
MOUNTING METHOD	Panel
USED WITH	low-peak finger safe fuse

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2209
MULTIMEDIA	The Power of Space Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TCFH100N
TECHNICAL DATA SHEETS	TCFH100N~CUBFUSE 100 AMP HOLDER HIGH PROFILE
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.