



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THQC2130WL 2P 30A 120/240V Circuit Breaker *Industrial Connections &*

|                  |  |
|------------------|--|
| Catalog Number   | THQC2130WL   |
| Manufacturer     | Industrial Connections &   |
| Description      | Q Line Circuit Breakers Are One-Inch Wide Per Pole, Compact, Thermal-Magnetic Devices Designed For Residential and Commercial Applications. The QC Breakers Are Lug-Lug Versions Of The Q Line and Are Available For 35MM Din Rail Mounting. All Q Line Circuit Breakers Feature Quick-Make / Quick-Break Mechanisms, Common Trip Bars, and Easy to Spot Trip Indication to Ensure Safety and Reliability. Q Line Breakers Are Available In 1, 2, and 3 Pole Versions and Can Be Ordered With Auxiliary Contact and Shunt Trip |
| Weight per unit  | 1,764.0 (lbs/each)   |
| Product Category | 2 Pole Din Rail Mount Circuit  |

### Features

|                  |                                 |
|------------------|---------------------------------|
| amperage rating  | 30A                             |
| frame            | Q-Line                          |
| interrupt rating | 10kA@120 Vac / 10kA@120/240 Vac |
| Load Rating      | HACR                            |
| Poles            | 2                               |
| trip range       | Non-Interchangeable             |
| Trip Type        | LI                              |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 2P 30A 120/240V CIRCUIT BREAKER  |
| extra long description | GE THQC2130WL CIRCUIT BREAKER 2P 3   |
| Long Description       | Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip |
| Product Type           | Circuit Breaker 2P 30A 120/240V 10ka   |
| Special Features       | Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | GE             |
| GTIN                      | 00783164012545 |
| Manufacturers Part Number | THQC2130WL     |
| UPC                       | 783164012545   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Loadcenter Plug In Breakers and Accessories |
|----------------------|---|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 1764 |

## Uses, Certifications, and Standards

|             |                |
|-------------|----------------|
| Application | Multi-terminal |
| standard    | E11592         |