



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THQP225 2POLE 25AMP Slimline *Industrial Connections &*

Catalog Number	THQP225
Manufacturer	Industrial Connections &
Description	THQP Breakers Are A Smaller, Smarter Solution For Today'S Cost- and Quality-Conscious Contractors and Homeowners. Half The Width and Identical In Design In Comparison to Standard Breakers, They Allow Use Of Smaller Load Centers and For Maximum Savings Of Space and Money. Ge Is The Only Manufacturer That Gives You This Cost Advantage Without Sacrificing Flexibility. The THQP225 Breaker Features A 1/2" Width, 2 Pole, An Ampere Rating Of 25 A, An Interrupting Rating Of 10KAIC, and A Voltage Rating Of 120/240V
Weight per unit	383.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	25 A
connection	14-8 kcmil / 12-8 kcmil
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
Poles	2
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	120/240 V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	2POLE 25AMP SLIMLINE
extra long description	GE THQP225 THQP 2 POLE 120/240V 10K
Long Description	THQP breakers are a smaller, smarter solution for today's cost- and quality-conscious contractors and homeowners. Half the width and identical in design in comparison to standard breakers, they allow use of smaller load centers and for maximum savings of space and money. GE is the only manufacturer that gives you this cost advantage without sacrificing flexibility. The THQP225 breaker features a 1/2" width, 2 pole, an ampere rating of 25 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V
Product Type	THQP 2 Pole 120/240V 10K Ic 25 Amp
Special Features	THQP breakers are a smaller, smarter solution for today's cost- and quality-conscious contractors and homeowners. Half the width and identical in design in comparison to standard breakers, they allow use of smaller load centers and for maximum savings of space and money. GE is the only manufacturer that gives you this cost advantage without sacrificing flexibility. The THQP225 breaker features a 1/2" width, 2 pole, an ampere rating of 25 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V

Manufacturer Information

Brand	GE
GTIN	00783164085662
Manufacturers Part Number	THQP225
UPC	783164085662

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
----------------------	---

Packaging

Carton	1
Weight Per each	383

Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592