



FLOOR BOX

TM1542BOX | [Pass & Seymour](#)

FEATURES & BENEFITS

Floor Box. 38 cubic inch, with knockouts and Auto/Clamps, three screws for mounting to floor. Gray.

- Hinged door is removable and easily replaceable.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed.
- Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Component Type: Full Assemblies

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 4.0"

Diameter (US): 5.5"

TECHNICAL INFORMATION

Floor Type: Wood

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





FLOOR BOX

TM1542BOX | [Pass & Seymour](#)

FEATURES & BENEFITS

Floor Box. 38 cubic inch, with knockouts and Auto/Clamps, three screws for mounting to floor. Gray.

- Hinged door is removable and easily replaceable.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed.
- Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Component Type: Full Assemblies

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 4.0"

Diameter (US): 5.5"

TECHNICAL INFORMATION

Floor Type: Wood

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

