



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMCX1001L Barr Gland 1 NPT SZ1 Alu

Crouse-Hinds

Catalog Number	TMCX1001L
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Terminator II TMCX Cable Gland, Liquid Compound, Cable Range:0.65-1.18", Cable Sealing:1 (S), Metal-Cladcorrugated Armoured, Teck Armoured, Armoured Barrier and Tray Cable, Armoured Gland, Aluminum, 1" NPT
Weight per unit	1.0 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Cable OD 0.65 to 1.18 inch
dimensions	4.2600 IN X 2.2500 IN X 2.2500 IN

Material, Color, and Finish

Color	Natural with red union nut
Finish	Untreated

Dimensions and Weight

Size	1" NPT, Size 1
------	----------------

Descriptions

Description	BARR GLAND 1 NPT SZ1 ALU
extra long description	CRS-H TMCX100 1 L BARR GLAND 1 NPT
Features	TMCX II explosionproof cable glands from Eaton Crouse-Hinds Division are used to terminate armoured barrier, non-armoured barrier and TECK armoured cable in hazardous locations. Its unique design features, coupled with our fast curing Chico LiquidSeal compound, make the TMCX II the easiest and safest solution available.
Long Description	Eaton Crouse-Hinds series Terminator II TMCX cable gland,Liquid compound,Cable Range:0.65-1.18",Cable Sealing:1 (S),Metal-cladcorrugated armoured,TECK armoured,armoured barrier and tray cable,Armoured gland, Aluminum, 1" NPT
Product Type	Barr Gland 1 NPT SZ1 Alu Liq
Special Features	2 Piece Union Design

Manufacturer Information

Brand	Eaton
GTIN	00662276303706
Manufacturers Part Number	TMCX100 1 L
UPC	662276303706



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting standard	1 inch NPT UL and cUL Class 1, Div 1 (ABCD) Class 2 (EFG)
Temperature Rating	-40 to + 60 Degrees C