



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TMCX1002 1" Cable Gland

*Crouse-Hinds*

Catalog Number	TMCX1002
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Terminator II TMCX Cable Gland, TSC Compound, Cable Range:0.87-1.39", Cable Sealing:2 (M), Metal-Cladcorrugated Armoured, Teck Armoured, Armoured Barrier and Tray Cable, Armoured Gland, Aluminum, 1" NPT
Weight per unit	1.1 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

### Features

connection	Cable OD 0.87 to 1.39 inch
dimensions	4.3800 IN X 2.5600 IN X 2.5600 IN

### Material, Color, and Finish

Color	Natural with red union nut
Finish	Untreated

### Dimensions and Weight

Size	1" NPT, Size 2
------	----------------

### Descriptions

Description	1" CABLE GLAND
extra long description	CRS-H TMCX100 2 BARR GLAND 1 NPT S
Features	TMCX II explosionproof cable glands from Eaton Crouse-Hinds Division are used to terminate armoured barrier, non-armoured barrier and TECK armoured cable in hazardous locations. Its unique design features, coupled with our fast curing Chico LiquidSeal compound, make the TMCX II the easiest and safest solution available.
Long Description	Eaton Crouse-Hinds series Terminator II TMCX cable gland,TSC compound,Cable Range:0.87-1.39",Cable Sealing:2 (M),Metal-cladcorrugated armoured,TECK armoured,armoured barrier and tray cable,Armoured gland, Aluminum, 1" NPT
Product Type	Barr Gland 1 NPT SZ2 Alu TSC
Special Features	2 Piece Union Design

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662276298170
Manufacturers Part Number	TMCX100 2
UPC	662276298170



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

## Packaging

Carton	1
Weight Per each	1.1499

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting	1 inch NPT
standard	UL and cUL Class 1, Div 1 (ABCD) Class 2 (EFG)
Temperature Rating	-40 to + 60 Degrees C