



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TP28 Trademaster Wallplate 3G 2 Toggle 1 Duplex BR

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | TP28 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Trademaster Plate 3-Gang, 2-Toggle, 1-Duplex Receptacle |
| Weight per unit | 0.1245 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|------------------------------------|
| cutout | Toggle and Receptacle |
| insulation | Bare |
| Mounting Type | Exposed Screws |
| Number of Gangs | 3 |
| orientation | Vertical |
| Wall Plate Type | Outlet, Dimmer/Switch, Combination |

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|---|
| Description | TRADEMASTER WALLPLATE 3G 2 TOGGLE 1 DUPLEX BR |
| extra long description | P&S TP28 TRADEMASTER PLATE 3G 2 TOG |
| Long Description | Trademaster Plate 3-Gang, 2-toggle, 1-duplex receptacle |
| Product Type | Trademaster Plate 3G 2 Tog 1 Dup BR |
| Special Features | Molded of rugged, practically indestructible nylon |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007275124 |
| Manufacturers Part Number | TP28 |
| UPC | 785007275124 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 15 |
| Package | 150 |
| Weight Per each | 0.1245 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CULUS, CSA, UL514 |