

# Specifications



## Eaton TP171

Eaton Crouse-Hinds series Switch Box, (1) 1/2", VP, set 1/2", 2, NM clamps, 2-1/2", (1) 1/2", Steel, (1) 1/2", Gangable, 12.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP171
<b>UPC</b>	786189101713
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.73 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>DEPTH</b>	2-1/2"
<b>TYPE</b>	Gangable
<b>CAPACITY</b>	12.5 cubic in
<b>CONDUIT/CABLE</b>	NM clamps

<b>BRACKET STYLE</b>	VP, Set 1/2"
<b>END KNOCKOUTS</b>	(1) 1/2 in
<b>SIDE KNOCKOUTS</b>	(1) 1/2 in
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>CABLE KNOCKOUTS</b>	2
<b>MATERIAL</b>	Steel

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Switch Boxes catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Switch Boxes Canadian certification</a> <a href="#">Steel Switch Boxes UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP171</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP171

Eaton Crouse-Hinds series Switch Box, (1) 1/2", VP, set 1/2", 2, NM clamps, 2-1/2", (1) 1/2", Steel, (1) 1/2", Gangable, 12.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP171
<b>UPC</b>	786189101713
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.73 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>DEPTH</b>	2-1/2"
<b>TYPE</b>	Gangable
<b>CAPACITY</b>	12.5 cubic in
<b>CONDUIT/CABLE</b>	NM clamps

<b>BRACKET STYLE</b>	VP, Set 1/2"
<b>END KNOCKOUTS</b>	(1) 1/2 in
<b>SIDE KNOCKOUTS</b>	(1) 1/2 in
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>CABLE KNOCKOUTS</b>	2
<b>MATERIAL</b>	Steel

## Resources

**CATALOGS** [Crouse-Hinds series Steel Switch Boxes catalog page](#)

**CERTIFICATION REPORTS** [Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

**SPECIFICATIONS AND DATASHEETS** [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP171](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

