

Specifications

Eaton TP377

Eaton Crouse-Hinds series Octagon Box and Adjustable Bar Set, 4", NM clamps, 1-1/2", Steel, Fixture rated, use with 4" octagon box, 16", 15.5 cubic inch capacity



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon box and adjustable bar set
CATALOG NUMBER	TP377
UPC	786189103779
PRODUCT LENGTH/DEPTH	16 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	1.02 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	NM clamps

STUD SPACING	16"
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated, use with 4" octagon box

Resources

CATALOGS	Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page
CERTIFICATION REPORTS	Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP377 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton TP377

Eaton Crouse-Hinds series Octagon Box and Adjustable Bar Set, 4", NM clamps, 1-1/2", Steel, Fixture rated, use with 4" octagon box, 16", 15.5 cubic inch capacity



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon box and adjustable bar set
CATALOG NUMBER	TP377
UPC	786189103779
PRODUCT LENGTH/DEPTH	16 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	1.02 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	NM clamps

STUD SPACING	16"
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated, use with 4" octagon box

Resources

CATALOGS	Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page
CERTIFICATION REPORTS	Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP377 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

