

# Eaton TP422

Catalog Number: TP422

Eaton Crouse-Hinds series Square Extension Ring, 4", Welded, 1-1/2", Steel, (8) 1/2", (4) 1/2", (1) 3/4" E, For use as extension with switch box, not 4 square box, 21.0 cubic inch capacity



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series square extension ring	TP422
	UPC
	786189104226
<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
4 in	0.5 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

21 cubic in

### Depth

1-1/2"

### Construction

Welded

### Side knockouts

(8) 1/2 in, (4) 1/2 in, (1) 3/4 in E

### Material

Steel

### Type

For use as extension with switch box, not 4 square box

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP422](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP422

Catalog Number: TP422

Eaton Crouse-Hinds series Square Extension Ring, 4", Welded, 1-1/2", Steel, (8) 1/2", (4) 1/2", (1) 3/4" E, For use as extension with switch box, not 4 square box, 21.0 cubic inch capacity



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series square extension ring	TP422
	UPC
	786189104226
<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
4 in	0.5 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

21 cubic in

### Depth

1-1/2"

### Construction

Welded

### Side knockouts

(8) 1/2 in, (4) 1/2 in, (1) 3/4 in E

### Material

Steel

### Type

For use as extension with switch box, not 4 square box

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP422](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)