

# Eaton TP266

Catalog Number: TP266

Eaton Crouse-Hinds series Round Ceiling Pan, 3-1/4", Bottom, 4, (1) 1/2", 1/2", Steel, Fixture rated, 4.0 cubic inch capacity

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series round ceiling pan	TP266
	UPC
	786189102666
Product Length/Depth	Product Height
3.25 in	0.25 in
Product Width	Product Weight
3.25 in	0.3 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

3-1/4"

### Depth

1/2"

### Capacity

4 cubic in

### Cable knockouts

4

### Conduit knockouts

(1) 1/2"

### Built-in clamps

Bottom

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP266](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP266

Catalog Number: TP266

Eaton Crouse-Hinds series Round Ceiling Pan, 3-1/4", Bottom, 4, (1) 1/2", 1/2", Steel, Fixture rated, 4.0 cubic inch capacity

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series round ceiling pan	TP266
	UPC
	786189102666
Product Length/Depth	Product Height
3.25 in	0.25 in
Product Width	Product Weight
3.25 in	0.3 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

3-1/4"

### Depth

1/2"

### Capacity

4 cubic in

### Cable knockouts

4

### Conduit knockouts

(1) 1/2"

### Built-in clamps

Bottom

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP266](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)