

Eaton TP266

Catalog Number: TP266

Eaton Crouse-Hinds series Round Ceiling Pan, 3-1/4", Bottom, 4, (1) 1/2", 1/2", Steel, Fixture rated, 4.0 cubic inch capacity

General specifications



| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series round ceiling pan | TP266 |
| | UPC |
| | 786189102666 |
| Product Length/Depth | Product Height |
| 3.25 in | 0.25 in |
| Product Width | Product Weight |
| 3.25 in | 0.3 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

3-1/4"

Depth

1/2"

Capacity

4 cubic in

Cable knockouts

4

Conduit knockouts

(1) 1/2"

Built-in clamps

Bottom

Material

Steel

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP266](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP266

Catalog Number: TP266

Eaton Crouse-Hinds series Round Ceiling Pan, 3-1/4", Bottom, 4, (1) 1/2", 1/2", Steel, Fixture rated, 4.0 cubic inch capacity

General specifications



| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series round ceiling pan | TP266 |
| | UPC |
| | 786189102666 |
| Product Length/Depth | Product Height |
| 3.25 in | 0.25 in |
| Product Width | Product Weight |
| 3.25 in | 0.3 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

3-1/4"

Depth

1/2"

Capacity

4 cubic in

Cable knockouts

4

Conduit knockouts

(1) 1/2"

Built-in clamps

Bottom

Material

Steel

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP266](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)