

# Specifications



## Eaton TP266

Eaton Crouse-Hinds series Round Ceiling Pan, 3-1/4", Bottom, 4, (1) 1/2", 1/2", Steel, Fixture rated, 4.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series round ceiling pan
<b>CATALOG NUMBER</b>	TP266
<b>UPC</b>	786189102666
<b>PRODUCT LENGTH/DEPTH</b>	3.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	3.25 in
<b>PRODUCT WEIGHT</b>	0.3 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	3-1/4"
<b>DEPTH</b>	1/2"
<b>CAPACITY</b>	4 cubic in
<b>CABLE KNOCKOUTS</b>	4

<b>CONDUIT KNOCKOUTS</b>	(1) 1/2"
<b>BUILT-IN CLAMPS</b>	Bottom
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Fixture rated

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification</a> <a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TP266</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
 All other trademarks are property of their respective owners.

© 2025 Eaton. All Rights Reserved.



# Specifications



## Eaton TP266

Eaton Crouse-Hinds series Round Ceiling Pan, 3-1/4", Bottom, 4, (1) 1/2", 1/2", Steel, Fixture rated, 4.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series round ceiling pan
<b>CATALOG NUMBER</b>	TP266
<b>UPC</b>	786189102666
<b>PRODUCT LENGTH/DEPTH</b>	3.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	3.25 in
<b>PRODUCT WEIGHT</b>	0.3 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	3-1/4"
<b>DEPTH</b>	1/2"
<b>CAPACITY</b>	4 cubic in
<b>CABLE KNOCKOUTS</b>	4

<b>CONDUIT KNOCKOUTS</b>	(1) 1/2"
<b>BUILT-IN CLAMPS</b>	Bottom
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Fixture rated

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification</a> <a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TP266</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
 All other trademarks are property of their respective owners.

© 2025 Eaton. All Rights Reserved.

