

Specifications

Eaton TP414

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 1/2", (4) 3/4", 22.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP414
UPC	786189104141
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.67 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	22 cubic in
DEPTH	1-1/2"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(8) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
-----------------	---

**CERTIFICATION
REPORTS**

[4-Inch Steel Square Outlet
Boxes, Covers, Extension
Rings Canadian certification](#)

[4-Inch Steel Square Outlet
Boxes, Covers, Extension
Rings UL certification](#)

**SPECIFICATIONS AND
DATASHEETS**

[Steel Outlet Boxes for
Electrical Systems](#)

[Eaton Specification Sheet -
TP414](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton TP414

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 1/2", (4) 3/4", 22.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP414
UPC	786189104141
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.67 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	22 cubic in
DEPTH	1-1/2"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(8) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
-----------------	---

**CERTIFICATION
REPORTS**

[4-Inch Steel Square Outlet
Boxes, Covers, Extension
Rings Canadian certification](#)

[4-Inch Steel Square Outlet
Boxes, Covers, Extension
Rings UL certification](#)

**SPECIFICATIONS AND
DATASHEETS**

[Steel Outlet Boxes for
Electrical Systems](#)

[Eaton Specification Sheet -
TP414](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

