

# Specifications



## Eaton TP632

Eaton Crouse-Hinds series Gang Box, (6) 1/2" and 3/4" concentric, VP, Conduit (no clamps), 2-1/2", (2) 1/2" and 3/4" concentric, Steel, Three-gang, (3) 1/2" and 3/4" concentric, Non-gangable, 46.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series gang box
<b>CATALOG NUMBER</b>	TP632
<b>UPC</b>	786189106329
<b>PRODUCT LENGTH/DEPTH</b>	5.56 in
<b>PRODUCT HEIGHT</b>	2.5 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.43 lb



*Powering Business Worldwide*

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>DEPTH</b>	2-1/2"
<b>TYPE</b>	Non-gangable
<b>NUMBER OF GANGS</b>	Three-gang
<b>CAPACITY</b>	46.5 cubic in

<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>BRACKET STYLE</b>	VP
<b>END KNOCKOUTS</b>	(2) 1/2 in and 3/4 in concentric
<b>SIDE KNOCKOUTS</b>	(3) 1/2 in and 3/4 in concentric
<b>BOTTOM KNOCKOUTS</b>	(6) 1/2 in and 3/4 in concentric
<b>MATERIAL</b>	Steel

## Resources

### CATALOGS

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

### CERTIFICATION REPORTS

[Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

### SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP632](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP632

Eaton Crouse-Hinds series Gang Box, (6) 1/2" and 3/4" concentric, VP, Conduit (no clamps), 2-1/2", (2) 1/2" and 3/4" concentric, Steel, Three-gang, (3) 1/2" and 3/4" concentric, Non-gangable, 46.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series gang box
<b>CATALOG NUMBER</b>	TP632
<b>UPC</b>	786189106329
<b>PRODUCT LENGTH/DEPTH</b>	5.56 in
<b>PRODUCT HEIGHT</b>	2.5 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.43 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>DEPTH</b>	2-1/2"
<b>TYPE</b>	Non-gangable
<b>NUMBER OF GANGS</b>	Three-gang
<b>CAPACITY</b>	46.5 cubic in

<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>BRACKET STYLE</b>	VP
<b>END KNOCKOUTS</b>	(2) 1/2 in and 3/4 in concentric
<b>SIDE KNOCKOUTS</b>	(3) 1/2 in and 3/4 in concentric
<b>BOTTOM KNOCKOUTS</b>	(6) 1/2 in and 3/4 in concentric
<b>MATERIAL</b>	Steel

## Resources

### CATALOGS

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

### CERTIFICATION REPORTS

[Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

### SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP632](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

