



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TPC300 3" Three Piece Coupling

Appleton/Oz Gedney

| | |
|------------------|--|
| Catalog Number | TPC300 |
| Manufacturer | Appleton/Oz Gedney |
| Description | Conduit Hardware, Couplings, Armored Cable, Type: Threaded, Trade Size: 3 Inch, For Use With: Rigid or Imc, Material: Malleable Iron |
| Weight per unit | 4.3 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

Features

| | |
|----------------|-------------------|
| connection | Threaded |
| Connector Type | Threaded Coupling |

Material, Color, and Finish

| | |
|-------|----------|
| Color | Metallic |
|-------|----------|

Dimensions and Weight

| | |
|--------|------|
| Length | 2.56 |
|--------|------|

Descriptions

| | |
|------------------------|--|
| Description | 3" THREE PIECE COUPLING |
| extra long description | EGS TPC-300 3 IN 3 PIECE CPLG |
| Long Description | Conduit Hardware, Couplings, Armored Cable, Type: Threaded, Trade Size: 3 Inch, For Use With: Rigid or IMC, Material: Malleable Iron |
| Product Type | 3 In 3 Piece CPLG |
| Special Features | 3 IN Trade Size Three Piece Coupling, For Use With Rigid and IMC Conduit |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Appleton |
| GTIN | 00687855404506 |
| Manufacturers Part Number | TPC-300 |
| UPC | 687855404506 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type | Three Piece Coupling |

Trade Size

| | |
|------------|---|
| Trade Size | 3 |
|------------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 4.33 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Provides threaded coupling between lengths of conduit and IMC elbows, where neither can be rotated |
| standard | NEMA: FB-1;UL Listed: E163167;UL Standard: 514B |